



| Part nº | R1 | Details | Max. flow (l/min) | A | C |
|--------------------|------------|-------------------------------|-------------------|-----|-----|
| FITCA10C10 | 3/4" BSP | Carton 10 µ | 70 | 93 | 146 |
| FITCA10C25 | 3/4" BSP | Cartón 25 µ | 80 | 93 | 146 |
| FITCA10T125 | 3/4" BSP | Metálico 125 µ/Metallic 125 µ | 100 | 93 | 146 |
| FITCA11C10 | 3/4" BSP | Carton 10 µ | 90 | 93 | 212 |
| FITCA11C25 | 3/4" BSP | Cartón 25 µ | 100 | 93 | 212 |
| FITCA11T125 | 3/4" BSP | Metálico 125 µ/Metallic 125 µ | 120 | 93 | 212 |
| FITCA20C10 | 1" 1/4 BSP | Cartón 10 µ | 140 | 130 | 180 |
| FITCA20C25 | 1" 1/4 BSP | Cartón 25 µ | 160 | 130 | 180 |
| FITCA20T125 | 1" 1/4 BSP | Metálico 125 µ/Metallic 125 µ | 200 | 130 | 180 |
| FITCA21C10 | 1" 1/4 BSP | Cartón 10 µ | 160 | 130 | 230 |
| FITCA21C25 | 1" 1/4 BSP | Cartón 25 µ | 180 | 130 | 230 |
| FITCA21T125 | 1" 1/4 BSP | Metálico 125 µ/Metallic 125 µ | 220 | 130 | 230 |

*** Review attached PDF***